

PRODUCT REQUIREMENT SHEET

See LV 75-032

| | |
|---------------------------|-----------------------------|
| MEASURING VOLTAGE | 235V (stabilisation 3 min.) |
| MEASURING POSITION | Horizontal |
| LIFE TEST POSITION | Vertical |
| BURNING POSITION | Any |
| SWITCHING CYCLE | Continuous |
| AGEING | 1h at rated voltage |

| | VALUE UNIT | TOLERANCE |
|--|------------------|-------------------------|
| WATTAGE | 1300W | ± 6 % |
| LIFE | 5000 h | average |
| COLOR TEMPERATURE Clear lamp HeLeN Lamp | 2500 K NA | ± 100 K |
| FLUX (HeLeN lamp) Clear lamp Reduction | xxxxx lm 95 % | Indicative value min |
| CAP INSULATION (WET) | 2000 V | mini |
| WEIGHT | 55 g | |

Project

| | | | | | | | | | | | | | | | |
|---|------|-------------------------|------|------|------------|---|----|--------------------|-------|----|------------|---|----|---|--|
| 1 | 0833 | 2 | 0833 | 3 | 0000 | 4 | | 5 | | 6 | | 7 | | 8 | |
| SUPERSEDES : | | HALOGEN LAMP | | | | | | 9245 869 44900 | | | 26/03/2012 | | | | |
| 9245 869 44900 | | INFRARED HeLeN | | | | | | 0833/000 | | | | | | | |
| 0833/000 p. 190-2 | | 15094Z 1300W 235V | | | | | | | | | | | | | |
| Of 15/09/2011 | | DOCUMENTATION | | UNIT | PROJ EUROP | 2 | SH | SH | 190-2 | 10 | | | A4 | | |
| REF. : PDM IRK 2011-046 | | | | mm | | | | | | | | | | | |
| NOM : J.P. CHARLIER | | VALIDATION : A. PICHARD | | | | | | DR. FISCHER Europe | | | | | | | |
| All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner. | | | | | | | | | | | | | | | |