

# HEINE BETA® 200 S LED Ophthalmoscope

# Superior aspherical optics now with LEDHQ illumination

: Ho LED NOW IN HEINE OLIALITY





- Aspherical optical system
- · LED in HQ with continuous brightness control
- · Aluminium frame system

#### BETA 200 S with 7 apertures



Cobalt blue filter, fixation star with polar coordinates, large spot, small spot, pinhole, slit, hemispot



With red-free filter

Exclusive dustproof design protects the precision optical components and ensures maintenance-free operation. The BETA200/200S Ophthalmoscopes are the only instruments with an aluminium frame system. Optical components are flush-mounted on a cast aluminum frame, eliminating misalignment and making the instrument shock-resistant. The BETA 200 S LED has virtually unlimited hours of working life (up to 100,000 hours). No need to ever replace bulbs. Maintenance-free for a lifetime.

- : Exclusive aspherical optical system (AOS) for more information see the bottom of page 034.
- : LED in HQ: The new standard in LED illumination defining optimal light intensity, homogeneity and colour rendering for the most accurate diagnosis. Red is red, blue is blue. Colour temperature: 3,500 K, Colour Rendering Index (CRI) > 97, special index for red colours (R9) > 93 on a maximum scale of 100.
- : Special optical interface to precisely integrate the LED illumination with the optical system to ensure bright, homogeneous light during examinations.
- : The BETA 200 S Ophthalmoscope accommodates higher refractive errors with a 28 single lenses Rekoss Disc and features a 74 single step design on a non-continuous wheel avoiding extreme diopter jumps.
  - + in 1D steps: +1 through +38D
  - in 1D steps: -1 through -36D
- : Exclusive continuous brightness control between 100 % and 3 % (patent pending) with one-finger operation.
- : No stray light due to the recessed, multi-coated viewing window eliminates distractions.
- : Precise one-hand control of the instrument. Ergonomic design offers flexibility while examining.
- : Suitable for large as well as small or undilated pupils.
- : Ergonomic design fits the orbita comfortably, and blocks out ambient light.
- : Full functionality of the BETA 200 S LED is guaranteed with BETA Recharcheable Handels and the EN100 Wall Transformer.

BETA 200 S LED Ophthalmoscope	LED
without handle	C-008.30.120

### HEINE BETA® 200 S Ophthalmoscope

### Superior aspherical optics with XHL illumination



BETA 200 S Ophthalmoscope with XHL Xenon Halogen illumination instead of LED illumination. Other technical specifications the same as the BETA 200 S LED Ophthalmoscope.

: XHL Xenon Halogen bulb with bright illumination and authentic colour rendering.

BETA 200 S Ophthalmoscope	2.5 V XHL	3.5V XHL
without handle	C-001.30.120	C-002.30.120
XHL Xenon Halogen spare bulb	X-001.88.069	X-002.88.070



# HEINE BETA® 200 LED Ophthalmoscope

### Superior aspherical optics now with LEDHQ illumination

The ophthalmoscope with unique aspherical optics and all features of the BETA 200 S LED, but:

- : Without macula aperture (pinhole)
- : The BETA 200 Ophthalmoscope accommodates higher refractive errors with a 27 single lenses Rekoss Disc.

+ in 1 D steps: 1 - 10				
- in 1 D steps: 1 - 10	15	20	25	35 D

BETA 200 LED Ophthalmoscope	LED
without handle	C-008.30.100

Full functionality of the BETA 200 LED is guaranteed with BETA Recharcheable Handels and the EN100 Wall Transformer.

# EXCLUSIVELY AT HEINE

· Aspherical optical system

LED NOW IN HEINE QUALITY.

- LED in HQ with continuous brightness control
- · Aluminium frame system

#### BETA 200 with 6 apertures



Slit, fixation star with polar coordinates, cobalt blue filter, large spot, small spot, hemispot




#### With red-free filter

# HEINE BETA® 200 Ophthalmoscope

### Superior aspherical optics with XHL illumination

The ophthalmoscope with unique aspherical optics and all features of the BETA 200 LED, but:

: XHL Xenon Halogen bulb with bright illumination and authentic colour rendering.



BETA 200 M2 Ophthalmoscope	2.5V XHL	3.5V XHL
BETA 200 M2 Ophthalmoscope, without handle.  Like BETA 200, except with pinhole instead		
of small spot and with fixation star aperture without		
polar coordinates.	C-001.30.102	C-002.30.102

#### BETA 200 M2 apertures











# HEINE BETA® 200/200 S Ophthalmic Diagnostic Sets





# Set complete with: **BETA 200 S Ophthalmoscope in XHL or LED** 1 spare bulb for XHL version, hard case

	BETA 200 S Ophthalmoscope Sets	2.5V XHL	3.5V XHL	LED
	BETA battery handle	C-261.10.118		
0	BETA4 USB rechargeable handle with			
	USB cord and plug-in power supply		C-261.27.388	C-261.28.388
0	BETA 4 USB rechargeable handle		C-261.27.387	C-261.28.387
0	BETA4 NT rechargeable handle			
	with NT4 table charger		C-261.23.420	C-261.24.420





8.388
8.387
4.420
8

 $<sup>^{\</sup>star}\text{Available with large battery handle \textbf{X-001.99.120}} \ (\text{doesn't fit into hard cases}). \ Please specify with your order.$ 

# Set complete with: **BETA200 S Ophthalmoscope in XHL or LED, BETA200 Streak Retinoscope**

1 spare bulb for each instrument for XHL version, hard case



	BETA 200 S Ophthalmoscope Sets	2.5V XHL	3.5V XHL	3.5 V XHL/LED*
•	BETA battery handle BETA 4 USB rechargeable handle with	C-262.10.118		
	USB cord and plug-in power supply		C-262.27.388	C-262.25.388
	BETA 4 USB rechargeable handle		C-262.27.387	C-262.25.387
	BETA4 NT rechargeable handle			
	with NT4 table charger		C-262.23.420	C-262.25.420

<sup>\*</sup>BETA200 Streak Retinoscope with XHL illumination and BETA200S LED Ophthalmoscope with LED illumination.

# Set complete with: **BETA 200 Ophthalmoscope in XHL or LED, BETA 200 Streak Retinoscope**

1 spare bulb for each instrument for XHL version, hard case

BETA 200 Ophthalmoscope Sets	2.5V XHL	3.5V XHL	3.5 V XHL/LED*
BETA battery handle	C-145.10.118		
BETA 4 USB rechargeable handle with			
USB cord and plug-in power supply		C-145.27.388	C-145.25.388
BETA 4 USB rechargeable handle		C-145.27.387	C-145.25.387
BETA4 NT rechargeable handle			
with NT4 table charger		C-145.23.420	C-145.25.420

 $<sup>{}^\</sup>star BETA 200 \ Streak \ Retinoscope \ with \ XHL \ illumination \ and \ BETA 200 \ LED \ Ophthalmoscope \ with \ LED \ illumination.$ 

New BETA4 Handle range – for more information see pages 120 – 122.



# **HEINE Diagnostic Sets**





# Set complete: BETA 200 Ophthalmoscope, BETA 200 F.O. Otoscope both with XHL or LED,

1 set of reusable tips (B-000.11.111) 5 of both AllSpec disposable tips 2.5 and 4 mm dia. one spare bulb each for XHL version hard case

	Diagnostic Sets	2.5 V XHL	3.5 V XHL	LED
	BETA battery handle	A-132.10.118		
	BETA4 USB rechargeable handle with			
	USB cord and plug-in power supply		A-132.27.388	A-132.28.388
0	BETA4 USB rechargeable handle		A-132.27.387	A-132.28.387
	BETA4 NT rechargeable handle			
	with NT4 table charger		A-132.23.420	A-132.24.420



#### Set complete: $\ensuremath{\mathsf{BETA200}}$ Ophthalmoscope in XHL or LED,

# BETA100 Diagnostic Otoscope

1 set of reusable specula (B-000.11.221) 10 UniSpec disposable tips 4 mm dia. (B-000.11.237) one spare bulb each for XHL version hard case

	Diagnostic Sets	2.5 V XHL	3.5V XHL	3,5 V XHL/LED*
	BETA battery handle	A-234.10.118		
	BETA4 USB rechargeable handle with			
	USB cord and plug-in power supply		A-234.27.388	A-234.25.388
0	BETA4 USB rechargeable handle		A-234.27.387	A-234.25.387
	BETA4 NT rechargeable handle			
	with NT4 table charger		A-234.23.420	A-234.25.420

<sup>\*</sup>BETA100 Otoscope with XHL illumination and BETA200 LED Ophthalmoscope with LED illumination.

New BETA4 Handle range – for more information see pages 120 – 122.