



product details

**L 18 W/77**

Product description: L 18 W/77  
 Product code: 4050300004235  
 Quantity: Sleeves (FLH) contains 1 Piece (PCE)

You can find this product in the eCatalog:

[http://catalog.myosram.com?~language=EN&~country=COM&it\\_p=4050300004235](http://catalog.myosram.com?~language=EN&~country=COM&it_p=4050300004235)

Country specific categorizations				
SEG number	8329492			
Certificates & standards				
EEL - Energy Label	B			
Additional product data				
Base (standard designation) [PICOS]	G13			
Recycling	Yes			
Colors & materials				
Rated lamp mercury content	3.0 mg			
Electrical data				
Nominal wattage	18 W			
Construction wattage	18 W			
Rated lamp efficacy (HF data)	Under clarification by authority and standardization body			
Dimensions & weight				
Tube diameter	26 mm			
Diameter	26.00 mm			
Length	590.00 mm			
Length with base excl. base pins/connect	590 mm			
Lifespan				
Lifespan	13000 h <sup>1)</sup>			
Light technical data				
Luminous flux at 25 °C	550 lm			
Luminous flux	550 lm			
Light color	77			
Light color as per EN 12464-1	FLUORA			
Packaging units				
Product code	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4050300004235	Sleeves contains 1 Piece	30,000 mm x 28,000 mm x 610,000 mm	98,000 g (0,000 g)	0,512 Cubic dec.
4008321205155	Shipping carton box contains 10 Piece	151,000 mm x 67,000 mm x 634,000 mm	1 134,000 g (0,000 g)	6,414 Cubic dec.



product details

**L 18 W/77**

**FLUORA - light for healthier plants and for aquariums**

The light from FLUORA fluorescent lamps has an emphasis at the blue and red ends of the spectrum so it is ideal for promoting photo-biological processes in plants. The result is healthier plants.

FLUORA lamps are used wherever plants do not receive enough natural daylight, for example over feature planting in shopping centres, offices, hotels and the home, and also for florist shops and greenhouses.

For more information on QUICKTRONIC electronic control gear go to [www.osram.com/QUICKTRONIC](http://www.osram.com/QUICKTRONIC)

<sup>1)</sup> With preheat ECG